



□□□□□

Eaton PVMA5LJ/UNV1

Eaton Crouse-Hinds series Champ Pro PVMA LED light fixture, 150W MH, 50/60 Hz, Heat and impact resistant glass lens, 5000 lumens, 122 lm/W, Die cast aluminum, Stanchion 25° angled, Type V optics, >0.90 PF, 1-1/2" trade size, 48W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Champ Pro PVMA LED light fixture
CATALOG NUMBER	PVMA5LJ/UNV1
UPC	662276822061
PRODUCT LENGTH/DEPTH	14.57 in
PRODUCT HEIGHT	11.26 in
PRODUCT WIDTH	7.86 in
PRODUCT WEIGHT	15.6 lb

Certifications and compliances	
AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC IEC

Product specifications	
LUMENS	5000
LUMENS PER WATT	75
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	Stanchion 25° angled
TRADE SIZE	1-1/2"
OPTICAL DISTRIBUTION	Type V
VOLTAGE RATING	120-277 Vac, 127-300 Vdc
FREQUENCY RATING	50/60 Hz
MATERIAL	Die cast aluminum
LENS MATERIAL	Heat and impact resistant glass
WATTAGE	48W
EQUIVALENT LUMINAIRE	150W MH
POWER FACTOR	> 0.90

3D CAD DRAWING PACKAGE	Eaton Crouse-Hinds PVMA5LJ/UNV1 3D drawing
	IM0454 - Champ Pro PVMA LED
	Champ Pro PVMA Low Bay Industrial LED
	Eaton Specification Sheet - PVMA5LJ/UNV1
	Crouse-Hinds series Global LED lighting portfolio Crouse-Hinds series industrial LED lighting solutions Crouse-Hinds series Champ Pro PVMA LED brochure
	Crouse-Hinds series Champ Pro PVMA LED catalog page
	Champ Pro PVMA Low Bay Industrial LED Light Fixtures UL certification
	Champ Pro PVMA Low Bay Industrial LED Light Fixtures Canadian certification

