



□□□□□

Eaton PVML-11-2TW-UNV1

Eaton Crouse-Hinds series Champ Pro PVML LED fixture, Cool white, 320W HID equivalent, No guard, Glass lens, 11000 lumens, 122 lm/W, Die cast aluminum, Wall mount, Type V, 3/4" trade size, 100-277 Vac, 127-250 Vdc, 92W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Champ Pro PVML LED light fixture
CATALOG NUMBER	PVML-11-2TW-UNV1
UPC	662276891326
PRODUCT LENGTH/DEPTH	13.96 in
PRODUCT HEIGHT	11.31 in
PRODUCT WIDTH	11.62 in
PRODUCT WEIGHT	23.7 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC IEC
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LUMENS	11000
LUMENS PER WATT	75
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	Wall
TRADE SIZE	100-240 Vac, 127-250 Vdc
OPTICAL DISTRIBUTION	Type V
GUARD TYPE	No guard
VOLTAGE RATING	100-277 Vac, 127-250 Vdc
FREQUENCY RATING	50/60 Hz
WATTAGE	92W
DIMMING	Dimmable driver
POWER FACTOR	> 0.90
EQUIVALENT LUMINAIRE	320W HID
MATERIAL	Die cast aluminum
LENS MATERIAL	Heat and impact resistant glass

3D 00

[SP3D Design Package -
Champ Pro PVML
Industrial LED Light
Fixtures](#)

000000

[IF 1882 - Champ VMVL and
PVML LED luminaires](#)

[IF 1888 - Champ VMVL and
PVML Driver Replacement](#)

00000000

[Champ Pro PVM Industrial
LED](#)

[Eaton Specification Sheet -
PVML-11-2TW-UNV1](#)

0000

[Crouse-Hinds series
industrial LED lighting
solutions](#)

[Crouse-Hinds series
Global LED lighting
portfolio](#)

[Crouse-Hinds series
Champ Pro PVML LED
Luminaires - 3,000 to
13,000 lumens brochure](#)

[Crouse-Hinds series DLC
approved lighting
products](#)

0000

[Crouse-Hinds series
Champ Pro PVML LED
luminaires - 3,000 to
13,000 lumens catalog
page](#)

0000

[Champ Pro PVML
Industrial LED Light
Fixtures Canadian
certification](#)

[EC Declaration of
Conformity - Crouse-Hinds
series Champ Pro PVML
LED Luminaires](#)

[Champ Pro PVML
Industrial LED Light
Fixtures UL certification](#)

