



□□□□□

Eaton PVML-13-UNV1-M2

Eaton Crouse-Hinds series Champ Pro PVML LED fixture, Cool white, 400W HID equivalent, No guard, Heat and impact resistant glass lens, 13000 lumens, 125 lm/W, Die cast aluminum, No mounting module, Type V, 100-277 Vac, 127-250 Vdc, 95W

□□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Champ Pro PVML LED light fixture
CATALOG NUMBER	PVML-13-UNV1-M2
UPC	662276972148
PRODUCT LENGTH/DEPTH	13 in
PRODUCT HEIGHT	13.13 in
PRODUCT WIDTH	12.75 in
PRODUCT WEIGHT	20.8 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC IEC
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LUMENS	13000
LUMENS PER WATT	125
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	No mounting module
OPTICAL DISTRIBUTION	Type V
GUARD TYPE	No guard
VOLTAGE RATING	100-277 Vac, 127-250 Vdc
FREQUENCY RATING	50/60 Hz
WATTAGE	95W
DIMMING	Dimmable driver
POWER FACTOR	> 0.90
EQUIVALENT LUMINAIRE	400W HID
MATERIAL	Die cast aluminum
LENS MATERIAL	Heat and impact resistant glass

3D 00

[SP3D Design Package -
Champ Pro PVML
Industrial LED Light
Fixtures](#)

000000

[IF 1888 - Champ VMVL and
PVML Driver Replacement](#)

[IF 1882 - Champ VMVL and
PVML LED luminaires](#)

00000000

[Champ Pro PVM Industrial
LED](#)

[Eaton Specification Sheet -
PVML-13-UNV1-M2](#)

0000

[Crouse-Hinds series
Champ Pro PVML LED
Luminaires - 3,000 to
13,000 lumens brochure](#)

[Crouse-Hinds series
industrial LED lighting
solutions](#)

[Crouse-Hinds series
Global LED lighting
portfolio](#)

[Crouse-Hinds series DLC
approved lighting
products](#)

0000

[Crouse-Hinds series
Champ Pro PVML LED
luminaires - 3,000 to
13,000 lumens catalog
page](#)

0000

[EC Declaration of
Conformity - Crouse-Hinds
series Champ Pro PVML
LED Luminaires](#)

[Champ Pro PVML
Industrial LED Light
Fixtures Canadian
certification](#)

[Champ Pro PVML
Industrial LED Light
Fixtures UL certification](#)

