

Eaton RS100H

Fuse accessory, Fuse-holder, low voltage, 100 A, AC 690 V, BS88/A4, 1P, BS, front connected, black, TCP, CE0 and L14-660 fuse-links, BS88-2, IEC 60269-2, IP20

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse holder
CATALOG NUMBER	RS100H
UPC	051712390842
PRODUCT LENGTH/DEPTH	100 mm
PRODUCT HEIGHT	139 mm
PRODUCT WIDTH	50 mm
PRODUCT WEIGHT	822.4 g
COMPLIANCES	Contact factory

AMPERAGE RATING	100 A
CONNECTION TYPE	Screwed terminal
FEATURES	Halogen free
NUMBER OF POLES	Single-pole
VOLTAGE RATING AT AC	660-690 V a.c.
VOLTAGE RATING AT DC	460 V d.c.
FUSE TYPE	TCP CEO
ACCESSORIES	RS100LOCK, RS100RED, P5372-10, TCA2
BUS-MOUNTING TYPE	No
CONNECTION	Front Connected
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Screw-on
VOLTAGE RATING	690 V
TYPE	fuse accessory
APPLICATION	general industrial applications
MODEL	Red Spot

DECLARATIONS OF CONFORMITY	eaton-low-voltage-british-standard-fuse-holder-declaration-of-conformity-uk251065en.pdf

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

