



## Eaton RS100PH

Fuse accessory, Fuse-holder, low voltage, 100 A, AC 690 V, BS88/A4, 1P, BS, front/back stud connected, black, fuse-links TCP, CE0 and L14-660, BS88-2, IEC 60269-2, IP20

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage british standard fuse holder
<b>CATALOG NUMBER</b>	RS100PH
<b>UPC</b>	051712418706
<b>PRODUCT LENGTH/DEPTH</b>	187 mm
<b>PRODUCT HEIGHT</b>	139 mm
<b>PRODUCT WIDTH</b>	50 mm
<b>PRODUCT WEIGHT</b>	921.6 g
<b>COMPLIANCES</b>	Contact factory

□□□□	
AMPERAGE RATING	100 A
CONNECTION TYPE	Connector M10
FEATURES	Halogen free
NUMBER OF POLES	Single-pole
FITTED WITH:	One back stud
VOLTAGE RATING AT AC	660-690 V a.c.
VOLTAGE RATING AT DC	460 V d.c.
FUSE TYPE	TCP CEO
ACCESSORIES	RS100LOCK, RS100RED, P5372-10, TCA2
BUS-MOUNTING TYPE	No
CONNECTION	Front/back stud connected
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Screw-on
VOLTAGE RATING	690 V
TYPE	fuse accessory
APPLICATION	general industrial applications
MODEL	Red Spot

□□	
DECLARATIONS OF CONFORMITY	<a href="#">eaton-low-voltage-british-standard-fuse-holder-declaration-of-conformity-uk251065en.pdf</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:



□□□□  
Eaton House  
30 Pembroke Road  
Dublin 4, □□□  
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

