



Eaton RS100PWH

Fuse accessory, Fuse-holder, low voltage, 100 A, AC 690 V, BS88/A4, 1P, BS, back stud connected, white, fuse-links TCP CEO L14-660

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse holder
CATALOG NUMBER	RS100PWH
UPC	051712418713
PRODUCT LENGTH/DEPTH	187 mm
PRODUCT HEIGHT	139 mm
PRODUCT WIDTH	50 mm
PRODUCT WEIGHT	1047.2 g
COMPLIANCES	Contact factory



Powering Business Worldwide

□□□□	
AMPERAGE RATING	100 A
CONNECTION TYPE	Connector M10
FEATURES	Halogen free
NUMBER OF POLES	Single-pole
FITTED WITH:	Two back studs
VOLTAGE RATING AT AC	660-690 V a.c.
VOLTAGE RATING AT DC	460 V d.c.
FUSE TYPE	TCP CEO
ACCESSORIES	RS100LOCK, RS100RED, P5372-10, TCA2
BUS-MOUNTING TYPE	No
CONNECTION	Back stud connected
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Screw-on
VOLTAGE RATING	690 V
TYPE	fuse accessory
APPLICATION	general industrial applications
MODEL	Red Spot

□□	
DECLARATIONS OF CONFORMITY	eaton-low-voltage-british-standard-fuse-holder-declaration-of-conformity-uk251065en.pdf

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□: