

Eaton RS20FGN

Fuse accessory, Fuse-holder, low voltage, 20 A, AC 690 V, BS88/A1, 1P, BS, back stud connected, flush mounted, green, fuse-link NITD, fuse-link NIT, BS88-2, IEC 60269-2, IP20

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse holder
CATALOG NUMBER	RS20FGN
UPC	051712418799
PRODUCT LENGTH/DEPTH	112 mm
PRODUCT HEIGHT	84 mm
PRODUCT WIDTH	38 mm
PRODUCT WEIGHT	224.7 g
COMPLIANCES	Contact factory

AMPERAGE RATING	20 A
CONNECTION TYPE	Other
FEATURES	Halogen free
NUMBER OF POLES	Single-pole
FITTED WITH:	Two back studs
VOLTAGE RATING AT AC	660-690 V a.c.
VOLTAGE RATING AT DC	460 V d.c.
FUSE TYPE	NITD NIT
ACCESSORIES	RS20LOCK, RS20RED
COLOR	Green
BUS-MOUNTING TYPE	No
CONNECTION	Back stud connected, flush mounted
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Screw-on
VOLTAGE RATING	690 V
TYPE	fuse accessory
APPLICATION	general industrial applications
MODEL	Red Spot

DECLARATIONS OF CONFORMITY	eaton-low-voltage-british-standard-fuse-holder-declaration-of-conformity-uk251065en.pdf

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

