

Eaton RS20FGY

Fuse accessory, Fuse-holder, low voltage, 20 A, AC 690 V, BS88/A1, 1P, BS, back stud connected, flush mounted, grey, fuse-link NITD, fuse-link NIT, BS88-2, IEC 60269-2, IP20

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse holder
CATALOG NUMBER	RS20FGY
UPC	051712418805
PRODUCT LENGTH/DEPTH	112 mm
PRODUCT HEIGHT	84 mm
PRODUCT WIDTH	38 mm
PRODUCT WEIGHT	213.4 g
COMPLIANCES	Contact factory

AMPERAGE RATING	20 A
CONNECTION TYPE	Other
FEATURES	Halogen free
NUMBER OF POLES	Single-pole
FITTED WITH:	Two back studs
VOLTAGE RATING AT AC	660-690 V a.c.
VOLTAGE RATING AT DC	460 V d.c.
FUSE TYPE	NITD NIT
ACCESSORIES	RS20LOCK, RS20RED
COLOR	Gray
BUS-MOUNTING TYPE	No
CONNECTION	Back stud connected, flush mounted
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Screw-on
VOLTAGE RATING	690 V
TYPE	fuse accessory
APPLICATION	general industrial applications
MODEL	Red Spot

DECLARATIONS OF CONFORMITY	eaton-low-voltage-british-standard-fuse-holder-declaration-of-conformity-uk251065en.pdf
-----------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

: