

Eaton RS20H

Fuse accessory, Fuse-holder, low voltage, 20 A, AC 690 V, BS88/A1, 1P, BS, front connected, Paint finish, NITD and NIT fuse-links, BS88-2, IEC 60269-2, IP20

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse holder
CATALOG NUMBER	RS20H
UPC	051712392587
PRODUCT LENGTH/DEPTH	55 mm
PRODUCT HEIGHT	79 mm
PRODUCT WIDTH	27 mm
PRODUCT WEIGHT	129.6 g
COMPLIANCES	Contact factory

AMPERAGE RATING	20 A
CONNECTION TYPE	Screwed terminal
FEATURES	Halogen free
NUMBER OF POLES	Single-pole
VOLTAGE RATING AT AC	660-690 V a.c.
VOLTAGE RATING AT DC	460 V d.c.
FUSE TYPE	NITD NIT
ACCESSORIES	RS20LOCK, RS20RED
COLOR	Black
BUS-MOUNTING TYPE	No
CONNECTION	Front Connected
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Screw-on
VOLTAGE RATING	690 V
TYPE	fuse accessory
APPLICATION	general industrial applications
MODEL	Red Spot

DECLARATIONS OF CONFORMITY	eaton-low-voltage-british-standard-fuse-holder-declaration-of-conformity-uk251065en.pdf
-----------------------------------	---

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
 30 Pembroke Road
 Dublin 4,
 Eaton.com
 © 2025

Follow us on social media to get the latest product and support information.