



Eaton RS20P-GWH

Eaton Bussmann series low voltage British standard fuse holder, LV, 20 A, AC 690 V, BS88/A1, 1P, BS, back stud connected, white

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse holder
CATALOG NUMBER	RS20P-GWH
UPC	051712418898
PRODUCT LENGTH/DEPTH	114 mm
PRODUCT HEIGHT	79 mm
PRODUCT WIDTH	27 mm
PRODUCT WEIGHT	182 g
COMPLIANCES	CE
CERTIFICATIONS	Not Applicable

□□□□	
AMPERAGE RATING	20 A
CONNECTION TYPE	Other
FEATURES	Halogen free
NUMBER OF POLES	Single-pole
FITTED WITH:	Two back studs
VOLTAGE RATING AT AC	660-690 V a.c.
VOLTAGE RATING AT DC	460 V d.c.
FUSE TYPE	NITD NIT
ACCESSORIES	RS20LOCK, RS20RED
COLOR	White
BUS-MOUNTING TYPE	No
CONNECTION	Back stud Back stud connected
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Screw-on
VOLTAGE RATING	660 V
TYPE	fuse accessory
APPLICATION	general industrial applications
MODEL	Red Spot

□□	
DECLARATIONS OF CONFORMITY	eaton-low-voltage-british-standard-fuse-holder-declaration-of-conformity-uk251065en.pdf

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:



□□□□
Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

