

Eaton RS32HGN

Fuse accessory, Fuse-holder, low voltage, 32 A, AC 690 V, BS88/A2, 1P, BS, front connected, green, fuse-links TIA, AA0 and H07-660, BS88-2, IEC 60269-2, IP20

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse holder
CATALOG NUMBER	RS32HGN
UPC	051712418935
PRODUCT LENGTH/DEPTH	70 mm
PRODUCT HEIGHT	103 mm
PRODUCT WIDTH	31 mm
PRODUCT WEIGHT	256 g
COMPLIANCES	Contact factory

AMPERAGE RATING	32 A
CONNECTION TYPE	Screwed terminal
FEATURES	Halogen free
NUMBER OF POLES	Single-pole
VOLTAGE RATING AT AC	660-690 V a.c.
VOLTAGE RATING AT DC	460 V d.c.
FUSE TYPE	TIA AAO
ACCESSORIES	RS32LOCK, RS32RED
COLOR	Green
BUS-MOUNTING TYPE	No
CONNECTION	Front Connected
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Screw-on
VOLTAGE RATING	690 V
TYPE	fuse accessory
APPLICATION	general industrial applications
MODEL	Red Spot

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-holder-declaration-of-conformity-uk251065en.pdf](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

