



Eaton RS32PH

Fuse accessory, Fuse-holder, low voltage, 32 A, AC 690 V, BS88/A2, 1P, BS, front connected, back stud connected, black, fuse-links TIA AAO H07-660

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse holder
CATALOG NUMBER	RS32PH
UPC	051712418973
PRODUCT LENGTH/DEPTH	179 mm
PRODUCT HEIGHT	173 mm
PRODUCT WIDTH	224 mm
PRODUCT WEIGHT	284.3 g
COMPLIANCES	Contact factory

□□□□	
AMPERAGE RATING	32 A
CONNECTION TYPE	Other
FEATURES	Halogen free
NUMBER OF POLES	Single-pole
FITTED WITH:	One back stud
VOLTAGE RATING AT AC	660-690 V a.c.
VOLTAGE RATING AT DC	460 V d.c.
FUSE TYPE	TIA AAO
ACCESSORIES	RS32LOCK, RS32RED
BUS-MOUNTING TYPE	No
CONNECTION	Front/back stud connected
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Screw-on
VOLTAGE RATING	690 V
TYPE	fuse accessory
APPLICATION	general industrial applications
MODEL	Red Spot

□□	
DECLARATIONS OF CONFORMITY	eaton-low-voltage-british-standard-fuse-holder-declaration-of-conformity-uk251065en.pdf

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□: