



Eaton RS63PHWH

Fuse accessory, Fuse-holder, low voltage, 63 A, AC 690 V, BS88/A3, 1P, BS, front/back stud connected, white, fuse-links TIS BAO K07-660, BS88-2, IEC 60269-2, IP20

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse holder
CATALOG NUMBER	RS63PHWH
UPC	051712419086
PRODUCT LENGTH/DEPTH	159 mm
PRODUCT HEIGHT	109 mm
PRODUCT WIDTH	35 mm
PRODUCT WEIGHT	411 g
COMPLIANCES	Contact factory

□□□□	
AMPERAGE RATING	63 A
CONNECTION TYPE	Connector M8
FEATURES	Halogen free
NUMBER OF POLES	Single-pole
FITTED WITH:	One back stud
VOLTAGE RATING AT AC	660-690 V a.c.
VOLTAGE RATING AT DC	460 V d.c.
FUSE TYPE	BAO TIS
ACCESSORIES	RS63LOCK, RS63RED
COLOR	White
BUS-MOUNTING TYPE	No
CONNECTION	Front/back stud connected
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Screw-on
VOLTAGE RATING	690 V
TYPE	fuse accessory
APPLICATION	general industrial applications
MODEL	Red Spot

□□	
DECLARATIONS OF CONFORMITY	eaton-low-voltage-british-standard-fuse-holder-declaration-of-conformity-uk251065en.pdf

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:



□□□□
Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

