

Eaton RS63PWH

Fuse accessory, Fuse-holder, low voltage, 63 A, AC 690 V, BS88/A3, 1P, BS, back stud connected, white, fuse-links TIS BAO K07-660

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse holder
CATALOG NUMBER	RS63PWH
UPC	051712419093
PRODUCT LENGTH/DEPTH	159 mm
PRODUCT HEIGHT	109 mm
PRODUCT WIDTH	35 mm
PRODUCT WEIGHT	460.1 g
COMPLIANCES	Contact factory

AMPERAGE RATING	63 A
CONNECTION TYPE	Connector M8
FEATURES	Halogen free
NUMBER OF POLES	Single-pole
FITTED WITH:	Two back studs
VOLTAGE RATING AT AC	660-690 V a.c.
VOLTAGE RATING AT DC	460 V d.c.
FUSE TYPE	BAO TIS
ACCESSORIES	RS63LOCK, RS63RED
BUS-MOUNTING TYPE	No
CONNECTION	Back stud connected
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Screw-on
VOLTAGE RATING	690 V
TYPE	fuse accessory
APPLICATION	general industrial applications
MODEL	Red Spot

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

