



# Eaton

## RT2SHEO200WLS3HIP

Eaton RoundTech Medium Surface Safety  
eFocus HIGHBAY WLS 200 lm MNM 3H IP65

□□□□

|                                 |                                                         |
|---------------------------------|---------------------------------------------------------|
| <b>PRODUCT NAME</b>             | Eaton RoundTech MSSEO<br>surface emergency<br>luminaire |
| <b>CATALOG NUMBER</b>           | RT2SHEO200WLS3HIP                                       |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 138 mm                                                  |
| <b>PRODUCT HEIGHT</b>           | 48 mm                                                   |
| <b>PRODUCT WIDTH</b>            | 138 mm                                                  |
| <b>PRODUCT WEIGHT</b>           | 0.3 kg                                                  |
| <b>CERTIFICATIONS</b>           | CE                                                      |

|                                            |                                                      |
|--------------------------------------------|------------------------------------------------------|
| BATTERY QUALITY                            | Lithium-ion                                          |
| PROTECTION CLASS                           | II                                                   |
| DEGREE OF PROTECTION                       | IP65                                                 |
| LAMP TYPE                                  | LED not exchangeable                                 |
| WITH LIGHT SOURCE                          | Yes                                                  |
| LAMP HOLDER                                | None                                                 |
| MONITORING EQUIPMENT                       | Safety module for monitoring (central feeded system) |
| POWER SUPPLY SYSTEM                        | Peripheral (individual battery)                      |
| VOLTAGE TYPE                               | AC                                                   |
| POWER FACTOR                               | 0.61                                                 |
| WITH REMOTE SWITCH CONNECTION              | No                                                   |
| ENERGY EFFICIENCY CLASS                    | A                                                    |
| CONDUCTOR CROSS SECTION                    | 2.5                                                  |
| CONNECTION TYPE                            | Plug-in connection                                   |
| MAX. SYSTEM POWER                          | 1.1 W                                                |
| TYPE OF CONTROL GEAR                       | LED operating device current-controlled              |
| TYPE OF WIRING                             | Suitable for through wiring                          |
| NOMINAL VOLTAGE AC - MAX                   | 230 V                                                |
| NOMINAL VOLTAGE AC - MIN                   | 230 V                                                |
| RATED AMBIENT TEMP ACC. IEC62722-2-1 - MIN | 5 °C                                                 |
| RATED AMBIENT TEMP ACC. IEC62722-2-1 - MAX | 45 °C                                                |
| NOMINAL OPERATION TIME - MIN               | 3 hour                                               |
| NOMINAL OPERATION TIME - MAX               | 3 hour                                               |
| SUITABLE FOR STANDBY SWITCHING             | No                                                   |
| SUITABLE FOR CONTINUOUS CIRCUIT            | No                                                   |
| RAL-NUMBER (SIMILAR) HOUSING               | 9003                                                 |
| MOUNTING METHOD                            | Ceiling surface mounting                             |
| MATERIAL HOUSING                           | Plastic                                              |
| COLOR HOUSING                              | White                                                |
| MATERIAL COVER                             | Without cover                                        |

|                                                    |                       |
|----------------------------------------------------|-----------------------|
| PICTOGRAM INCLUDED                                 | No                    |
| NUMBER OF POLES (NUMERIC)                          | 3                     |
| OUTER DIAMETER                                     | 138 mm                |
| IMPACT STRENGTH                                    | IK04                  |
| RATED LUMINOUS FLUX ACC. IEC 62722-2-1             | 200 lm                |
| COLOR TEMPERATURE - MAX                            | 5700 K                |
| COLOR TEMPERATURE - MIN                            | 5700 K                |
| LIGHT DISTRIBUTOR                                  | Focal lens            |
| FUNCTION                                           | Escape route lighting |
| LUMINAIRE WITH LIMITED SURFACE TEMPERATURE, SIGN D | No                    |
| LUMINOUS FLUX IN STANDBY MODE                      | 60 lm                 |
| NUMBER OF LIGHTING HEADS                           | 1                     |
| PRODUCT BRANDING                                   | Eaton                 |
| WITH REMOTE CONTROL                                | No                    |
| CONSTANT LIGHT OUTPUT (CLO)                        | No                    |
| EXCHANGEABLE CONTROL GEAR                          | No                    |

|  |
|--|
|  |
|  |
|  |
|  |