

Eaton S20K11E02P

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 60 Hz, single-phase, 240V X 480V, 120/240 V, Shielded, 1 at -10% X 2 at -5%, 115 °C rise, 2 KVA, indoor-outdoor,

PRODUCT NAME	Eaton General purpose encapsulated transformer
CATALOG NUMBER	S20K11E02P
UPC	786680234927
PRODUCT LENGTH/DEPTH	6 in
PRODUCT HEIGHT	10.75 in
PRODUCT WIDTH	6.32 in
PRODUCT WEIGHT	45 lb
COMPLIANCES	Not Applicable
CERTIFICATIONS	UL Listed

SPECIAL FEATURES	Shielded
TYPE	General-Purpose Encapsulated Transformer
COIL MATERIAL	Aluminum
FREQUENCY RATING	60 Hz
KVA RATING	2 kVA
KVA	2 kVA
MOUNTING	Wall Mount
PHASE	Single-phase
PRIMARY VOLTAGE	240 V, 480 V
SECONDARY VOLTAGE	120/240 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	115 °C rise
DESIGN	EP
ENCLOSURE	NEMA 3R
FRAME	68P
INSULATION	180 °C
TAP SIZE	1 at -10% FCBN x 2 at -5% FCBN
VOLT AMPERE RATING	2 kVA
WEATHERSHIELD	Indoor-Outdoor
WIRING CONNECTION	21A

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

