



□□□□□

Eaton S20L11S25CUSS4X

Eaton General-purpose encapsulated transformer EP Single-phase 240 x 480V 2 at -5% FCBN x 4 at -2.5% FCBN 120/240V 150°C 25 kVA Copper windings 1824X 23A Indoor-Outdoor 60 Hz NEMA 4X

□□□□

PRODUCT NAME	Eaton General purpose encapsulated transformer
CATALOG NUMBER	S20L11S25CUSS4X
UPC	786680116148
PRODUCT LENGTH/DEPTH	15.1 in
PRODUCT HEIGHT	19.85 in
PRODUCT WIDTH	19.87 in
PRODUCT WEIGHT	450 lb
COMPLIANCES	Class I, Div. 2, Groups A, B, C, D Not Applicable
CERTIFICATIONS	UL Listed
CATALOG NOTES	NEMA 4X Grade 304 stainless steel enclosure.

□□□□	
TYPE	General-purpose encapsulated transformer
COIL MATERIAL	Copper
FREQUENCY RATING	60 Hz
KVA RATING	25 kVA
KVA	25 kVA
MOUNTING	Wall Mount
PHASE	Single-phase
PRIMARY VOLTAGE	240 V, 480 V
SECONDARY VOLTAGE	120/240 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	115 °C rise
VOLTAGE RATING	240 X 480 PV, 120/240 SV
DESIGN	EP
ENCLOSURE	NEMA 4X
FRAME	1824X
INSULATION	180C
TAP SIZE	2 at -5% FCBN x 4 at -2.5% FCBN
VOLT AMPERE RATING	25 kVA
WEATHERSHIELD	Indoor-Outdoor
WIRING CONNECTION	23A

□□	
□□□□□□□□	Eaton Specification Sheet - S20L11S25CUSS4X

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:



□□□□
Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 □□ □□□□□□□□

Follow us on social media to get the latest product and support information.

