



## Eaton SC20BH

Fuse accessory, Fuse-holder, low voltage, 20 A, AC 550 V, BS88/E1, 1P, BS, busbar/front connected, fuse-link SSD, BS88-2, Optional accessories copper links, padlockable inserts and adaptor carriers

### □□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage british standard fuse holder
<b>CATALOG NUMBER</b>	SC20BH
<b>UPC</b>	051712419383
<b>PRODUCT LENGTH/DEPTH</b>	25 mm
<b>PRODUCT HEIGHT</b>	59 mm
<b>PRODUCT WIDTH</b>	71 mm
<b>PRODUCT WEIGHT</b>	132 g
<b>COMPLIANCES</b>	Contact factory



*Powering Business Worldwide*

□□□□	
AMPERAGE RATING	20 A
CONNECTION TYPE	Other
FEATURES	Halogen free
NUMBER OF POLES	Single-pole
VOLTAGE RATING AT AC	550 V a.c.
FUSE TYPE	SSD
COLOR	Black
BUS-MOUNTING TYPE	No
CONNECTION	Busbar/front connected
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Screw-on
TYPE	fuse accessory
APPLICATION	general industrial applications
MODEL	Safeclip

□□	
DECLARATIONS OF CONFORMITY	<a href="#">eaton-low-voltage-british-standard-fuse-holder-declaration-of-conformity-uk251100en.pdf</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:



□□□□  
Eaton House  
30 Pembroke Road  
Dublin 4, □□□  
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

