



Eaton SC20HGN

Fuse accessory, Fuse-holder, low voltage, 20 A, AC 550 V, BS88/E1, 1P, BS, front connected, green, fuse-link SSD, BS88-2, Optional accessories copper links, padlockable inserts and adaptor carriers

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse holder
CATALOG NUMBER	SC20HGN
UPC	051712419406
PRODUCT LENGTH/DEPTH	71 mm
PRODUCT HEIGHT	47 mm
PRODUCT WIDTH	25 mm
PRODUCT WEIGHT	94.8 g
COMPLIANCES	Contact factory

□□□□	
AMPERAGE RATING	20 A
CONNECTION TYPE	Other
FEATURES	Halogen free
NUMBER OF POLES	Single-pole
VOLTAGE RATING AT AC	550 V a.c.
FUSE TYPE	SSD
ACCESSORIES	SSC-LINK, DIN-20-32
COLOR	Green
BUS-MOUNTING TYPE	No
CONNECTION	Front Connected
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Screw-on
TYPE	fuse accessory
APPLICATION	general industrial applications
MODEL	Safeclip

□□	
DECLARATIONS OF CONFORMITY	eaton-low-voltage-british-standard-fuse-holder-declaration-of-conformity-uk251100en.pdf

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:



□□□□
Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

