

## Eaton SC20PWH

Fuse accessory, Fuse-holder, low voltage, 20 A, AC 550 V, BS88/E1, 1P, BS, back stud connected, white, fuse-link SSD, BS88-2, Optional accessories copper links, padlockable inserts and adaptor carriers

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage british standard fuse holder
<b>CATALOG NUMBER</b>	SC20PWH
<b>UPC</b>	051712419444
<b>PRODUCT LENGTH/DEPTH</b>	25 mm
<b>PRODUCT HEIGHT</b>	87 mm
<b>PRODUCT WIDTH</b>	71 mm
<b>PRODUCT WEIGHT</b>	94.8 g
<b>COMPLIANCES</b>	Contact factory

<b>AMPERAGE RATING</b>	20 A
<b>CONNECTION TYPE</b>	Other
<b>FEATURES</b>	Halogen free
<b>NUMBER OF POLES</b>	Single-pole
<b>FITTED WITH:</b>	Two back studs
<b>VOLTAGE RATING AT AC</b>	550 V a.c.
<b>FUSE TYPE</b>	SSD
<b>COLOR</b>	White
<b>BUS-MOUNTING TYPE</b>	No
<b>CONNECTION</b>	Back stud connected
<b>CONSTRUCTION SIZE</b>	Other
<b>MOUNTING METHOD</b>	Screw-on
<b>TYPE</b>	fuse accessory
<b>APPLICATION</b>	general industrial applications
<b>MODEL</b>	Safeclip

<b>DECLARATIONS OF CONFORMITY</b>	<a href="#">eaton-low-voltage-british-standard-fuse-holder-declaration-of-conformity-uk251100en.pdf</a>
-----------------------------------	---

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
:



Eaton House  
 30 Pembroke Road  
 Dublin 4,  
 Eaton.com  
 © 2025

Follow us on social media to get the latest product and support information.

