



Eaton SC32H/DGN

Fuse accessory, Fuse-holder, low voltage, 32 A, AC 550 V, BS88/E1, 1P, BS, front connected, green, fuse-link NSD, BS88-2, Optional accessories copper links, padlockable inserts and adaptor carriers

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse holder
CATALOG NUMBER	SC32H/DGN
UPC	051712419468
PRODUCT LENGTH/DEPTH	81 mm
PRODUCT HEIGHT	52 mm
PRODUCT WIDTH	25 mm
PRODUCT WEIGHT	96.7 g
COMPLIANCES	CE
CERTIFICATIONS	Not Applicable



Powering Business Worldwide

SC32H	
AMPERAGE RATING	32 A
CONNECTION TYPE	Other
FEATURES	Halogen free
NUMBER OF POLES	Single-pole
VOLTAGE RATING AT AC	550 V a.c.
FUSE TYPE	NSD
ACCESSORIES	NSC-LINK, SC32LOCK, DIN-20-32
COLOR	Green
BUS-MOUNTING TYPE	No
CONNECTION	Front Front Connected
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Screw-on
VOLTAGE RATING	550 V
TYPE	fuse accessory
APPLICATION	general industrial applications
MODEL	Safeclip

SC32H	
DECLARATIONS OF CONFORMITY	eaton-low-voltage-british-standard-fuse-holder-declaration-of-conformity-uk251100en.pdf
SC32H/DGN	SC32H/DGN

SC32H:
SC32H:
SC32H:
SC32H: