



□□□□

## Eaton SDQ12-330-R

Eaton SDQ inductor, 32.49 uH, 0.22 A Irms, 0.267 A ISAT, 3000 mΩ resistance, SMT mounting, Ferrite, 4-pins, 3800 qty.

□□□□

<b>PRODUCT NAME</b>	Eaton SDQ12 inductor
<b>CATALOG NUMBER</b>	SDQ12-330-R
<b>UPC</b>	051712890151
<b>PRODUCT LENGTH/DEPTH</b>	5.2 mm
<b>PRODUCT HEIGHT</b>	1.2 mm
<b>PRODUCT WIDTH</b>	5.2 mm
<b>PRODUCT WEIGHT</b>	0.11 g
<b>COMPLIANCES</b>	RoHS Compliant



Powering Business Worldwide

