



## Eaton SMD2

Eaton Bussmann series low voltage british standard fuse, 2A, AC 415 V, 13 x 29 mm, gL/gG

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage british standard fuse
<b>CATALOG NUMBER</b>	SMD2
<b>PRODUCT LENGTH/DEPTH</b>	29 mm
<b>PRODUCT HEIGHT</b>	16 mm
<b>PRODUCT WIDTH</b>	16 mm
<b>PRODUCT WEIGHT</b>	12.1 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	BS88 IEC 60269 EAC

□□□□	
AMPERAGE RATING	2 A
CURRENT TYPE	AC
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	10 kA
RATED VOLTAGE AC	415 V
CLASS	Class gG/gL
FUSE TYPE	SMD
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	1 W
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION	BS88
CONSTRUCTION SIZE	Other
FUSE SHAPE	Cylindrical
VOLTAGE TYPE	AC
VOLTAGE RATING	415 V
TYPE	Fuse
APPLICATION	street lighting cut-outs
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:

□□	
DECLARATIONS OF CONFORMITY	<a href="#">eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk251015en.pdf</a>



□□□□  
 Eaton House  
 30 Pembroke Road  
 Dublin 4, □□□  
 Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

