

# Eaton SMS12P24PDH1NA

Plug 12P24 with 8 power & 4 standard TRIM TRIO contacts; SMS12P24PDH1NA

<b>PRODUCT NAME</b>	Eaton Souriau SMS series quick mating plastic rectangular connector
<b>CATALOG NUMBER</b>	SMS12P24PDH1NA
<b>PRODUCT LENGTH/DEPTH</b>	32.6 mm
<b>PRODUCT HEIGHT</b>	36.9 mm
<b>PRODUCT WIDTH</b>	18.6 mm
<b>PRODUCT WEIGHT</b>	12.5 g

ENVIRONMENTAL CONDITIONS	REACH
	RoHS
	Flammability rating UL94
	V0
BACKSHELL TYPE	Strain Relief
CONNECTOR ACCESSORY OPTION	Integrated with connector
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT TYPE	Crimp
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP30
LAYOUT	12
PLUG TYPE	Straight Plug
SHELL MATERIAL	Plastic
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-55 °C
NUMBER OF CONTACTS	12
NUMBER OF CAVITY #12	8
NUMBER OF CAVITY #16	4

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

