

Eaton SMS12RDH2NA

Receptacle 12 with 8 power & 4 standard TRIM TRIO contacts; SMS12RDH2NA

PRODUCT NAME	Eaton Souriau SMS series quick mating plastic rectangular connector
CATALOG NUMBER	SMS12RDH2NA
PRODUCT LENGTH/DEPTH	52.7 mm
PRODUCT HEIGHT	25.1 mm
PRODUCT WIDTH	16.2 mm
PRODUCT WEIGHT	8.3 g

ENVIRONMENTAL CONDITIONS	REACH Flammability rating UL94 V0 RoHS
--------------------------	--

BACKSHELL TYPE	Strain Relief
----------------	---------------

CONNECTOR ACCESSORY OPTION	Integrated with connector
----------------------------	---------------------------

CONNECTOR TYPE	Receptacle
----------------	------------

CONTACT DELIVERY	Not delivered
------------------	---------------

CONTACT TYPE	Crimp
--------------	-------

COUPLING TYPE	Push-Pull
---------------	-----------

DEGREE OF PROTECTION	IP30
----------------------	------

LAYOUT	12
--------	----

SHELL MATERIAL	Plastic
----------------	---------

OPERATING TEMPERATURE - MAX	125 °C
-----------------------------	--------

OPERATING TEMPERATURE - MIN	-55 °C
-----------------------------	--------

RECEPTACLE TYPE	Free Hanging
-----------------	--------------

NUMBER OF CONTACTS	12
--------------------	----

NUMBER OF CAVITY #12	8
----------------------	---

NUMBER OF CAVITY #16	4
----------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:
