

Eaton SMS15RD3

Flame retardant receptacle without strain relief hood; SMS15RD3

PRODUCT NAME	Eaton Souriau SMS series quick mating plastic rectangular connector
CATALOG NUMBER	SMS15RD3
PRODUCT LENGTH/DEPTH	32.9 mm
PRODUCT HEIGHT	28.7 mm
PRODUCT WIDTH	18.6 mm
PRODUCT WEIGHT	8.8 g

ENVIRONMENTAL CONDITIONS	REACH
	Flammability rating UL94
	V0
	RoHS
	Fire & Smoke

CONNECTOR ACCESSORY OPTION	No backshell possibility
-------------------------------	--------------------------

CONNECTOR TYPE	Receptacle
----------------	------------

CONTACT DELIVERY	Not delivered
------------------	---------------

CONTACT TYPE	Crimp
--------------	-------

COUPLING TYPE	Push-Pull
---------------	-----------

DEGREE OF PROTECTION	IP40
----------------------	------

LAYOUT	15
--------	----

SHELL MATERIAL	Plastic
----------------	---------

OPERATING TEMPERATURE - MAX	105 °C
--------------------------------	--------

OPERATING TEMPERATURE - MIN	-40 °C
--------------------------------	--------

RECEPTACLE TYPE	Free Hanging
-----------------	--------------

NUMBER OF CONTACTS	15
--------------------	----

NUMBER OF CAVITY #16	15
----------------------	----

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

