

Eaton SMS15SE3T

Straight boardmount with short PCB female contacts (Tin plating); SMS15SE3T

PRODUCT NAME	Eaton Souriau SMS series quick mating plastic rectangular connector
CATALOG NUMBER	SMS15SE3T
PRODUCT LENGTH/DEPTH	13.4 mm
PRODUCT HEIGHT	16.2 mm
PRODUCT WIDTH	26.1 mm
PRODUCT WEIGHT	10.1 g

ENVIRONMENTAL CONDITIONS	Flammability rating UL94 V0 REACH
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Tin pre plated
CONTACT TYPE	PCB
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP30
LAYOUT	15
SHELL MATERIAL	Plastic
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-55 °C
RECEPTACLE TYPE	Front Mount Panel
NUMBER OF CONTACTS	15
NUMBER OF CAVITY #16	15

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

