



□□□□□

Eaton SMS18SE5T

Right angle boardmount with female contacts (Tin plating); SMS18SE5T

□□□□

PRODUCT NAME	Eaton Souriau SMS series quick mating plastic rectangular connector
CATALOG NUMBER	SMS18SE5T
PRODUCT LENGTH/DEPTH	29.5 mm
PRODUCT HEIGHT	17.2 mm
PRODUCT WIDTH	45.4 mm
PRODUCT WEIGHT	15 g

ENVIRONMENTAL CONDITIONS	Flammability rating UL94 V0 REACH
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Tin pre plated
CONTACT TYPE	PCB 90°
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP30
LAYOUT	18
SHELL MATERIAL	Plastic
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-55 °C
RECEPTACLE TYPE	Front Mount Panel
NUMBER OF CONTACTS	18
NUMBER OF CAVITY #16	18

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

00: