



□□□□□

Eaton SMS24SE3T

Straight boardmount with short PCB female contacts (Tin plating); SMS24SE3T

□□□□

PRODUCT NAME	Eaton Souriau SMS series quick mating plastic rectangular connector
CATALOG NUMBER	SMS24SE3T
PRODUCT LENGTH/DEPTH	13.4 mm
PRODUCT HEIGHT	21.2 mm
PRODUCT WIDTH	31.2 mm
PRODUCT WEIGHT	15.2 g

ENVIRONMENTAL CONDITIONS	REACH Flammability rating UL94 V0
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Tin pre plated
CONTACT TYPE	PCB
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP30
LAYOUT	24
SHELL MATERIAL	Plastic
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-55 °C
RECEPTACLE TYPE	Front Mount Panel
NUMBER OF CONTACTS	24
NUMBER OF CAVITY #16	24

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

00: