

Eaton SMS2R3

Flame retardant panel mount receptacle;
SMS2R3

PRODUCT NAME	Eaton Souriau SMS series quick mating plastic rectangular connector
CATALOG NUMBER	SMS2R3
PRODUCT LENGTH/DEPTH	25 mm
PRODUCT HEIGHT	15.2 mm
PRODUCT WIDTH	11 mm
PRODUCT WEIGHT	1.6 g

ENVIRONMENTAL CONDITIONS	REACH
	Flammability rating UL94
	V0
	Fire & Smoke
	RoHS

CONNECTOR ACCESSORY OPTION	No backshell possibility
-------------------------------	--------------------------

CONNECTOR TYPE	Receptacle
----------------	------------

CONTACT DELIVERY	Not delivered
------------------	---------------

CONTACT TYPE	Crimp
--------------	-------

COUPLING TYPE	Push-Pull
---------------	-----------

DEGREE OF PROTECTION	IP40
----------------------	------

LAYOUT	2
--------	---

SHELL MATERIAL	Plastic
----------------	---------

OPERATING TEMPERATURE - MAX	105 °C
--------------------------------	--------

OPERATING TEMPERATURE - MIN	-40 °C
--------------------------------	--------

RECEPTACLE TYPE	Front Mount Panel
-----------------	-------------------

NUMBER OF CONTACTS	2
--------------------	---

NUMBER OF CAVITY #16	2
----------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

