

Eaton SMS2RE4TR29

Straight boardmount with long PCB male contacts (Gold & Tin plating); SMS2RE4TR29

PRODUCT NAME	Eaton Souriau SMS series quick mating plastic rectangular connector
CATALOG NUMBER	SMS2RE4TR29
PRODUCT LENGTH/DEPTH	13.4 mm
PRODUCT HEIGHT	11 mm
PRODUCT WIDTH	5.9 mm
PRODUCT WEIGHT	2.2 g

ENVIRONMENTAL CONDITIONS	Flammability rating UL94 V0 REACH
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT PLATING	Tin pre plated
CONTACT TYPE	PCB
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP30
LAYOUT	2
SHELL MATERIAL	Plastic
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-55 °C
RECEPTACLE TYPE	Front Mount Panel
NUMBER OF CONTACTS	2
NUMBER OF CAVITY #16	2

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

