

Eaton SMS2SE4T

Straight boardmount with short PCB male contacts (Tin plating); SMS2SE4T

PRODUCT NAME	Eaton Souriau SMS series quick mating plastic rectangular connector
CATALOG NUMBER	SMS2SE4T
PRODUCT LENGTH/DEPTH	13.4 mm
PRODUCT HEIGHT	11 mm
PRODUCT WIDTH	5.9 mm
PRODUCT WEIGHT	2.2 g

ENVIRONMENTAL CONDITIONS	REACH Flammability rating UL94 V0
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Tin pre plated
CONTACT TYPE	PCB
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP30
LAYOUT	2
SHELL MATERIAL	Plastic
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-55 °C
RECEPTACLE TYPE	Front Mount Panel
NUMBER OF CONTACTS	2
NUMBER OF CAVITY #16	2

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

