

Eaton SMS36RE4TR29

Straight boardmount with long PCB male contacts (Gold & Tin plating); SMS36RE4TR29

PRODUCT NAME	Eaton Souriau SMS series quick mating plastic rectangular connector
CATALOG NUMBER	SMS36RE4TR29
PRODUCT LENGTH/DEPTH	13.4 mm
PRODUCT HEIGHT	46.5 mm
PRODUCT WIDTH	20.9 mm
PRODUCT WEIGHT	25.3 g

ENVIRONMENTAL CONDITIONS	Flammability rating UL94 V0 REACH
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT PLATING	Tin pre plated
CONTACT TYPE	PCB
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP30
LAYOUT	36
SHELL MATERIAL	Plastic
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-55 °C
RECEPTACLE TYPE	Front Mount Panel
NUMBER OF CONTACTS	36
NUMBER OF CAVITY #16	36

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

