

Eaton SMS4RDH3

Flame retardant receptacle with integrated strain relief hood; SMS4RDH3

PRODUCT NAME	Eaton Souriau SMS series quick mating plastic rectangular connector
CATALOG NUMBER	SMS4RDH3
PRODUCT LENGTH/DEPTH	49.2 mm
PRODUCT HEIGHT	9.9 mm
PRODUCT WIDTH	21.2 mm
PRODUCT WEIGHT	4.4 g

ENVIRONMENTAL CONDITIONS	Fire & Smoke Flammability rating UL94 V0 REACH RoHS
--------------------------	--

BACKSHELL TYPE	Strain Relief
----------------	---------------

CONNECTOR ACCESSORY OPTION	Integrated with connector
----------------------------	---------------------------

CONNECTOR TYPE	Receptacle
----------------	------------

CONTACT DELIVERY	Not delivered
------------------	---------------

CONTACT TYPE	Crimp
--------------	-------

COUPLING TYPE	Push-Pull
---------------	-----------

DEGREE OF PROTECTION	IP40
----------------------	------

LAYOUT	4
--------	---

SHELL MATERIAL	Plastic
----------------	---------

OPERATING TEMPERATURE - MAX	105 °C
-----------------------------	--------

OPERATING TEMPERATURE - MIN	-40 °C
-----------------------------	--------

RECEPTACLE TYPE	Free Hanging
-----------------	--------------

NUMBER OF CONTACTS	4
--------------------	---

NUMBER OF CAVITY #16	4
----------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

