

Eaton SMS4RE4TR29

Straight boardmount with long PCB male contacts (Gold & Tin plating); SMS4RE4TR29

PRODUCT NAME	Eaton Souriau SMS series quick mating plastic rectangular connector
CATALOG NUMBER	SMS4RE4TR29
PRODUCT LENGTH/DEPTH	13.4 mm
PRODUCT HEIGHT	21.3 mm
PRODUCT WIDTH	5.9 mm
PRODUCT WEIGHT	3.3 g

ENVIRONMENTAL CONDITIONS	REACH Flammability rating UL94 V0
--------------------------	--------------------------------------

CONNECTOR ACCESSORY OPTION	No backshell possibility
----------------------------	--------------------------

CONNECTOR TYPE	Receptacle
----------------	------------

CONTACT DELIVERY	Loaded
------------------	--------

CONTACT PLATING	Tin pre plated
-----------------	----------------

CONTACT TYPE	PCB
--------------	-----

COUPLING TYPE	Push-Pull
---------------	-----------

DEGREE OF PROTECTION	IP30
----------------------	------

LAYOUT	4
--------	---

SHELL MATERIAL	Plastic
----------------	---------

OPERATING TEMPERATURE - MAX	125 °C
-----------------------------	--------

OPERATING TEMPERATURE - MIN	-55 °C
-----------------------------	--------

RECEPTACLE TYPE	Front Mount Panel
-----------------	-------------------

NUMBER OF CONTACTS	4
--------------------	---

NUMBER OF CAVITY #16	4
----------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

