



Eaton SMS6SE3K9

Straight boardmount with short PCB female contacts (Gold & Tin plating); SMS6SE3K9

□□□□

PRODUCT NAME	Eaton Souriau SMS series quick mating plastic rectangular connector
CATALOG NUMBER	SMS6SE3K9
PRODUCT LENGTH/DEPTH	13.4 mm
PRODUCT HEIGHT	16.2 mm
PRODUCT WIDTH	10.9 mm
PRODUCT WEIGHT	4.7 g

ENVIRONMENTAL CONDITIONS	REACH
	RoHS
	Flammability rating UL94
	V0
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP30
LAYOUT	6
SHELL MATERIAL	Plastic
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-55 °C
RECEPTACLE TYPE	Front Mount Panel
NUMBER OF CONTACTS	6
NUMBER OF CAVITY #16	6

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

00: