



□□□□□

Eaton SR18UB

SmartRack 18U Mid-Depth Half-Height Rack
Enclosure Cabinet

□□□□

PRODUCT NAME	Eaton Tripp Lite series SmartRack rack enclosure
CATALOG NUMBER	SR18UB
UPC	037332178039
PRODUCT LENGTH/DEPTH	33.5 in
PRODUCT HEIGHT	35.6 in
PRODUCT WIDTH	23.62 in
PRODUCT WEIGHT	105 lb
COMPLIANCES	RoHS EIA-310-E UKCA
CERTIFICATIONS	UL 60950-1

SR18UB		SR18UB	
FEATURES	Flex Center		
COLOR	Black		
LOAD CAPACITY (DYNAMIC)	1000 lb		
LOAD CAPACITY (STATIC)	1000 lb		
MATERIAL	Steel		
PACKAGE CONTENTS	• SR18UB 18U Server Rack • (42) M6 screws • (42) M6 cage nuts • (42) M6 washers • (4) Casters • (4) Levelers • (2) Keys • Owner's manual		
PRODUCT FEATURES	Built-in Cable Management Locking Extra Wide Pre-Installed Casters		
RACK DEPTH	Mid		
PRODUCT HIGHLIGHTS	Provides physical equipment and media security required for PCI DSS compliance Ships fully assembled for immediate deployment and equipment mounting Maximum capacity: 1000 lb. (454 kg) stationary and rolling load Doors and side panels lock securely to help prevent damage, tampering or theft 18U rack constructed from powder-coated steel that stands up to tough environments 5-year limited warranty (Worldwide)		
RACK HEIGHT	18U		
CABLE ACCESS HOLE MEASUREMENT	9.812 x 2.35 (l x w)		
MAXIMUM DEVICE DEPTH	32.5 Inch		
NUMBER OF VERTICAL MOUNTING RAILS	4		
CABLE ENTRY/EXIT	9.812 x 2.35 (l x w)		
FACTORY PRESET RACK DEPTH	28.31 in		

MINIMUM DEVICE DEPTH	3 in
WEIGHT CAPACITY ROLLING	1000 lb
GROUNDING DETAILS	Front and Back door frames
WEIGHT CAPACITY STATIONARY	1000 Pound
MODULE RACK TYPE	Half-height enclosure
