



Eaton SR42UB

SmartRack 42U Standard-Depth Rack
Enclosure Cabinet with Doors and Side
Panels

□□□□

PRODUCT NAME	Eaton Tripp Lite series SmartRack rack enclosure
CATALOG NUMBER	SR42UB
UPC	037332123770
PRODUCT LENGTH/DEPTH	43 in
PRODUCT HEIGHT	78.5 in
PRODUCT WIDTH	23.63 in
PRODUCT WEIGHT	286 lb
COMPLIANCES	EIA-310-E RoHS CE Marked
CERTIFICATIONS	UL 60950-1



Powering Business Worldwide



FEATURES	Flex Center
COLOR	Black
LOAD CAPACITY (DYNAMIC)	2250 lb
LOAD CAPACITY (STATIC)	3500 lb
MATERIAL	Steel
NUMBER OF RACK UNITS	42U

PACKAGE CONTENTS

- SR42UB 42U Server Rack
- (4) Side panels
- (4) Side panel locks
- (2) Keys
- (50) M6 screws
- (50) M6 washers
- (50) M6 cage nuts
- Owner's manual

PRODUCT FEATURES	Extra Wide Locking Built-in Cable Management Pre-Installed Casters
-------------------------	--

RACK DEPTH	Standard
-------------------	----------

PRODUCT HIGHLIGHTS	42U rack constructed from powder-coated steel that stands up to tough environments Doors and side panels lock securely to help prevent damage, tampering or theft Provides physical equipment and media security required for PCI DSS compliance Maximum capacity: 3500 lb. (1588 kg) stationary, 2250 lb. (1021 kg) rolling load Ships fully assembled for immediate deployment and equipment mounting
---------------------------	---

RACK HEIGHT	42U
--------------------	-----

MAXIMUM DEVICE DEPTH	37 Inch
-----------------------------	---------

NUMBER OF VERTICAL MOUNTING RAILS	4
--	---

FACTORY PRESET RACK DEPTH	27.75 in
----------------------------------	----------

MINIMUM DEVICE DEPTH	4 in
-----------------------------	------

WEIGHT CAPACITY	2250 lb
------------------------	---------

