



Eaton SRFAN3UDCTEMP

3U Digital Temperature Sensor with 2 12VDC
Extra-Quiet Fans, Blanking Panel, LCD

□□□□

PRODUCT NAME	Eaton Tripp Lite series SmartRack blanking panel
CATALOG NUMBER	SRFAN3UDCTEMP
UPC	037332240637
PRODUCT LENGTH/DEPTH	2.62 in
PRODUCT HEIGHT	5.22 in
PRODUCT WIDTH	18.87 in
PRODUCT WEIGHT	5.11 lb
COMPLIANCES	RoHS



Powering Business Worldwide

INPUT CONNECTION	NEMA 1-15P
INPUT CORD LENGTH	6 ft
INPUT PLUG FEATURES	NEMA 1-15P
NOMINAL INPUT VOLTAGE DESCRIPTION	120V AC 60 Hz
AIR FLOW	169.00 CFM
INPUT FREQUENCY	60 Hz
SOUND LEVEL	33.8 dB
ACCESSORY CLASS	
ACCESSORY TYPE	Temperature sensor
COOLING TYPE	Active
PACKAGE CONTENTS	Temperature sensor 12V DC power supply with 6-ft. (1.83 m) cord and NEMA 1-15P plug Rack-mounting hardware SRFAN3UDCTEMP 3U Blanking Panel with Extra-Quiet Fans Owner's manual
INPUT NOMINAL VOLTAGE	120 VAC 120V AC 60 Hz
PRODUCT FEATURES	NEMA 1-15P
PRODUCT HIGHLIGHTS	Included temperature sensor identifies hot spots within the rack up to 6-ft. (1.83 m) away Pre-installed extra-quiet 4 in. 12VDC fans push cool air through the rack Cools rack equipment to boost system performance and avoid costly downtime Front-panel LCD displays rack temperature in Fahrenheit or Celsius 2-year limited warranty (Worldwide) Mounts easily into 3U of space in your EIA-standard 19 in. rack enclosure
RACK HEIGHT	3U
VOLTAGE RATING	120 VAC
