



## Eaton SRH42UWDPWD8

SmartRack 42U Deep Extra-Wide Heavy-Duty  
Rack Enclosure Cabinet for AI Servers -  
White

□□□□

|                                 |                                                     |
|---------------------------------|-----------------------------------------------------|
| <b>PRODUCT NAME</b>             | Eaton Tripp Lite series<br>SmartRack rack enclosure |
| <b>CATALOG NUMBER</b>           | SRH42UWDPWD8                                        |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 49.15 in                                            |
| <b>PRODUCT HEIGHT</b>           | 79.64 in                                            |
| <b>PRODUCT WIDTH</b>            | 31.5 in                                             |
| <b>PRODUCT WEIGHT</b>           | 540 lb                                              |
| <b>COMPLIANCES</b>              | CE Marked<br>EIA-310-E<br>RoHS<br>UKCA              |
| <b>CERTIFICATIONS</b>           | UL 62368-1<br>UL 2416                               |

|                         |                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|-------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| SRH42UWDPWD8            |                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| COLOR                   | White                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| LOAD CAPACITY (DYNAMIC) | 3500 lb                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| LOAD CAPACITY (STATIC)  | 5000 lb                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| MATERIAL                | Steel                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| NUMBER OF RACK UNITS    | 42U                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| PACKAGE CONTENTS        | <ul style="list-style-type: none"><li>• SRH42UWDPWD8 42U Server Rack</li><li>• (4) Side panels</li><li>• (4) Side panel locks</li><li>• (2) Keys</li><li>• (60) Phillips-head mounting screws (M6 x 5/8 in.)</li><li>• (60) Nylon cup washers</li><li>• (60) Cage nuts</li><li>• Owner's manual</li></ul>                                                                                                                                        |
| PRODUCT HIGHLIGHTS      | <p>Maximum capacity: 5000 lb. (2268 kg) stationary, 3500 lb. (1588 kg) rolling load</p> <p>2.5 mm thick steel frame includes extra welds and gussets for greater strength</p> <p>White powder-coated finish makes it easier to see ports and cables inside</p> <p>46 in. depth designed to accommodate large network and edge computing equipment</p> <p>Extra wide to allow side channels for accessory mounting, cable routing and airflow</p> |
| LOAD CAPACITY           | 5000 lb                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| CASTERS                 | Yes                                                                                                                                                                                                                                                                                                                                                                                                                                              |



