



Eaton SRW12US

SmartRack 12U Low-Profile Switch-Depth
Wall-Mount Small Rack Enclosure, Hinged
Back

□□□□

PRODUCT NAME	Eaton Tripp Lite series SmartRack rack enclosure
CATALOG NUMBER	SRW12US
UPC	037332148674
PRODUCT LENGTH/DEPTH	21.625 in
PRODUCT HEIGHT	24.625 in
PRODUCT WIDTH	23.5 in
PRODUCT WEIGHT	60 lb
WARRANTY	5 year limited
COMPLIANCES	EIA-310-E RoHS

□□□□	
FEATURES	Flex Center
COLOR	Black
LOAD CAPACITY (STATIC)	200 lb
MOUNTING LEVEL	Swing frame
PACKAGE CONTENTS	• SRW12US SmartRack 12U Low-Profile Switch-Depth Wall-Mount Rack Enclosure Cabinet • (20) M6 screws • (20) M6 cage nuts • (20) M6 washers • (20) 12-24 screws • (2) Keys • Owner's manual
RACK DEPTH	Shallow
PRODUCT HIGHLIGHTS	Flow-through ventilation keeps equipment cool Swings away from wall on hinge for easy back-door access 5-year limited warranty (Worldwide) Maximum load capacity of 200 lbs (90.7 kgs) Secures 12U of 19 in. rack equipment up to 20.5 in. deep Locking steel cabinet vented at sides, front, top and bottom
RACK HEIGHT	12U
CABLE ACCESS HOLE MEASUREMENT	9.812 x 2.35 (l x w)
MAXIMUM DEVICE DEPTH	20.5 Inch
NUMBER OF VERTICAL MOUNTING RAILS	4
CABLE ENTRY/EXIT	9.812 x 2.35 (l x w)
FACTORY PRESET RACK DEPTH	10.42 in
MINIMUM DEVICE DEPTH	3 in
GROUNDING DETAILS	Front and Back door frames
WEIGHT CAPACITY STATIONARY	200 Pound
MODULE RACK TYPE	Small Enclosure



