



Eaton SSD4

Eaton Bussmann series low voltage british standard fuse, 4A, AC 240 V, V88/E1, 12 x 47 mm, gL/gG

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	SSD4
UPC	051712841290
PRODUCT LENGTH/DEPTH	47 mm
PRODUCT HEIGHT	12 mm
PRODUCT WIDTH	12 mm
PRODUCT WEIGHT	11.6 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS88 IEC 60269-2

□□□□

AMPERAGE RATING	4 A
FITTED WITH:	Offset bladed tags
FUSE SIZE	BS88/E1
CURRENT TYPE	AC
BREAKING CAPACITY	33 kA
RATED SWITCHING CAPACITY	33 kA
RATED VOLTAGE AC	240 V
CLASS	Class gG/gL
FUSE TYPE	SSD
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	33 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	1 W
CONNECTION	Blade end
CONSTRUCTION	BS88/E1
CONSTRUCTION SIZE	E1
FUSE SHAPE	Offset bladed tags
VOLTAGE TYPE	AC
SUITABLE FOR	SC20 Safeclip fuse holder
VOLTAGE RATING	240 V
TYPE	Fuse
APPLICATION	street lighting cut-outs
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

□□

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk251015en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

