



Eaton SU6000RT4UHVPM

SmartOnline 6000VA Power Module - Hot-swappable replacement power module

□□□□

PRODUCT NAME	Eaton Tripp Lite series power module
CATALOG NUMBER	SU6000RT4UHVPM
UPC	037332151803
PRODUCT LENGTH/DEPTH	28.5 in
PRODUCT HEIGHT	12 in
PRODUCT WIDTH	23.5 in
PRODUCT WEIGHT	108 lb
COMPLIANCES	FCC Class A RoHS
CERTIFICATIONS	IEC/EN 62040-1 CSA certified UL 1778 NOM



Powering Business Worldwide

RACK SIZE	4U
PACKAGE CONTENTS	• SU6000RT4UHVPM power module with internal batteries • 4POSTRAILKIT mounting kit • USB, Serial and EPO cabling • PowerAlert Software
INPUT FREQUENCY RANGE	50/60 Hz
BATTERY REPLACEMENT	RBC5-192
ACCESSORY CLASS	UPS Accessories
ACCESSORY TYPE	Power Module
PRODUCT HIGHLIGHTS	Ideal for use as a spare or replacement power module for mission-critical UPS configurations involving several 6kVA UPS configurations 2-year limited warranty (Worldwide) 6000VA on-line 4U rack/tower hot-swappable replacement power module
BATTERY ACCESS	Front panel battery access door
BATTERY REPLACEMENT DESCRIPTION	Hot-swappable, user replaceable internal batteries
INTERNAL UPS REPLACEMENT BATTERY CARTRIDGE	RBC5-192
DC VOLTAGE	192
MINIMUM REQUIRED RACK DEPTH	24 in
SWITCHES	2 Switches control off/on power status and alarm-cancel/self-test operation; 2 additional switches support set and execute scrolling LCD functions

