



Eaton SUPDMB6KHW

Detachable PDU option for compatible SmartOnline UPS Systems, Hardwired Input/Output

□□□□

PRODUCT NAME	Eaton Tripp Lite series bypass panel
CATALOG NUMBER	SUPDMB6KHW
UPC	037332153739
PRODUCT LENGTH/DEPTH	3.19 in
PRODUCT HEIGHT	3.3 in
PRODUCT WIDTH	17.2 in
PRODUCT WEIGHT	6.6 lb
COMPLIANCES	FCC Compliant RoHS REACH CE Marked
CERTIFICATIONS	CSA certified UL 1778

PACKAGE CONTENTS	SUPDMB6KHW detachable PDU
INPUT CONNECTION	Hardwire
INPUT NOMINAL VOLTAGE	200 VAC/208 VAC/220 VAC/230 VAC/240 VAC
INPUT FREQUENCY RANGE	50/60 Hz
RECEPTACLE	Hardwire
OUTPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240V)
ACCESSORY CLASS	UPS Accessories
SYSTEM REQUIREMENTS	Requires SU6000RT4UHVPM UPS power module in any 200-240V AC configuration
ACCESSORY TYPE	PDU Module
PRODUCT HIGHLIGHTS	Can also be used to convert any high voltage UPS configuration using the SU6000RT4UHVPM power module to include hardwire output Detachable PDU backplate with manual bypass switch serves as a replacement PDU for configured SU6000RT4UHVHW and SU6000RT4UTFHW UPS systems Attaches via unit-specific back panel electrical and bolt-on connections Hardwire input and output supported Manual bypass feature ensures maximum equipment availability 2-year limited warranty (Worldwide)
MATERIAL OF CONSTRUCTION	Metal

