



Eaton SUPDMB710IEC

Detachable PDU option with IEC output connections for compatible SmartOnline UPS Systems

□□□□

PRODUCT NAME	Eaton Tripp Lite series circuit breaker
CATALOG NUMBER	SUPDMB710IEC
UPC	037332143594
PRODUCT LENGTH/DEPTH	9.6 in
PRODUCT HEIGHT	13.4 in
PRODUCT WIDTH	9.4 in
PRODUCT WEIGHT	7.9 lb
COMPLIANCES	RoHS CE Marked REACH FCC Compliant
CERTIFICATIONS	UL 1778 CSA certified

PACKAGE CONTENTS

- SUPDMB710IEC detachable PDU
- Mounting hardware
- Owner's Manual with warranty instructions

INPUT CONNECTION	Hardwire
INPUT NOMINAL VOLTAGE	200 VAC/208 VAC/220 VAC/230 VAC/240 VAC
INPUT FREQUENCY RANGE	50/60 Hz
RECEPTACLE	C19
OUTPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240V)
SYSTEM REQUIREMENTS	For use with SmartOnline SU8000RT3U and SU10000RT3U Rack/Tower UPS systems in applications requiring a detachable PDU with manual bypass
PRODUCT HIGHLIGHTS	Converts compatible SmartOnline high-voltage UPS systems to provide worldwide compatible output connections Hardwired input/ 6 IEC320 C19 output connections Manual bypass feature ensures maximum equipment availability For use with input voltages of 200-240 VAC
MATERIAL OF CONSTRUCTION	Metal
OVERLOAD PROTECTION	6 double-pole 20A circuit breakers

