



□□□□□

Eaton TBC4

Eaton Bussmann series low voltage british standard fuse, 4A, AC 660 V, DC 460 V, 27 x 129 mm, gL/gG

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	TBC4
PRODUCT LENGTH/DEPTH	27 mm
PRODUCT HEIGHT	27 mm
PRODUCT WIDTH	129 mm
PRODUCT WEIGHT	91.75 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS88 IEC 60269 EAC

□□□□

AMPERAGE RATING	4 A
FITTED WITH:	Centre bolted tags
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	111 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	460 V
CLASS	Class gG/gL
FUSE TYPE	TBC
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	111 mm fixing centre
CONSTRUCTION	BS88
CONSTRUCTION SIZE	Other
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC/DC
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

DECLARATIONS OF
CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250883en.pdf](#)

