



□□□□□

Eaton TCP100M200A

Eaton Bussmann series low voltage british standard fuse, 100 A, AC 660 V, DC 460 V, V88/A4, 26 x 110 mm, gM

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	TCP100M200A
UPC	051712485135
PRODUCT LENGTH/DEPTH	111 mm
PRODUCT HEIGHT	34 mm
PRODUCT WIDTH	34 mm
PRODUCT WEIGHT	197.7 g
COMPLIANCES	Not Applicable
CERTIFICATIONS	IEC Rated

0000

USED WITH	RS100H fuse holder
AMPERAGE RATING	100 A
FITTED WITH:	Offset bolted tags
FUSE SIZE	BS88/A4
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	93.7 mm
BREAKING CAPACITY	80 kA
MOTOR CURRENT RATING	100M200
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	460 V
CLASS	Class gM
FUSE TYPE	TCP
UTILIZATION CATEGORY	gM (motor protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
CONNECTION	94 mm fixing centre
CONSTRUCTION	BS88/A4
CONSTRUCTION SIZE	A4
FUSE SHAPE	Offset slotted bolted tags
VOLTAGE TYPE	AC/DC
SUITABLE FOR	RS100 Red spot fuse holder
PACKAGING TYPE	Standard
QUANTITY	10
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

□□

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk250883en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

