



Eaton TFC160

Eaton Bussmann series low voltage british standard fuse, 160A, AC 1500 V, DC 660 V, 40 x 192 mm, gL/gG

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	TFC160
UPC	051712392853
PRODUCT LENGTH/DEPTH	215 mm
PRODUCT HEIGHT	47 mm
PRODUCT WIDTH	48 mm
PRODUCT WEIGHT	497 g
COMPLIANCES	Contact Manufacturer



Powering Business Worldwide

□□□□

AMPERAGE RATING	160 A
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M10
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	168.4 mm
BREAKING CAPACITY	63 kA
RATED SWITCHING CAPACITY	63 kA
RATED VOLTAGE AC	1500 V
RATED VOLTAGE DC	660 V
CLASS	Class gG/gL
FUSE TYPE	TFC
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	63 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	Bolt-on
CONSTRUCTION SIZE	Other
FUSE SHAPE	Offset bolted tags
VOLTAGE TYPE	AC/DC
VOLTAGE RATING	1500 V
TYPE	Fuse
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□□□:

□□□□:

□□□:

□□:

00

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk250890en.pdf](#)