

Eaton TIS63

Eaton Bussmann series low voltage british standard fuse, 63A, AC 660 V, DC 460 V, V88/A3, 22 x 86 mm, gL/gG

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	TIS63
UPC	051712392976
PRODUCT LENGTH/DEPTH	84.5 mm
PRODUCT HEIGHT	21 mm
PRODUCT WIDTH	21 mm
PRODUCT WEIGHT	49.5 g
COMPLIANCES	Contact Manufacturer

AMPERAGE RATING	63 A
FITTED WITH:	Offset bolted tags
FUSE SIZE	BS88/A3
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M5
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	73 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	460 V
CLASS	Class gG/gL
FUSE TYPE	TIS
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	73 mm fixing centre
CONSTRUCTION	BS88/A3
CONSTRUCTION SIZE	A3
FUSE SHAPE	Offset bolted tags
VOLTAGE TYPE	AC/DC
SUITABLE FOR	CM63F Camaster fuse holder RS63 Red spot fuse holder
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250883en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

