



Eaton TKF315M355

Eaton Bussmann series low voltage british standard fuse, 315A, AC 660 V, DC 460 V, V88/B3, 53 x 137 mm, gM, 315M355

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	TKF315M355
UPC	051712484794
PRODUCT LENGTH/DEPTH	137 mm
PRODUCT HEIGHT	53 mm
PRODUCT WIDTH	53 mm
PRODUCT WEIGHT	498 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS88 IEC 60269 KEMA EAC

□□□□

AMPERAGE RATING	355 A
FITTED WITH:	Centre bolted tags
FUSE SIZE	BS88/B3
CURRENT TYPE	AC/DC
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	111 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
MOTOR CURRENT RATING	315M355
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	460 V
CLASS	Class gM
FUSE TYPE	TKF
UTILIZATION CATEGORY	gM (motor protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	111 mm fixing centre
CONSTRUCTION	BS88/B3
CONSTRUCTION SIZE	Other
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC/DC
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

□□

DECLARATIONS OF
CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250884en.pdf](#)

